

BDBLHC1123502, 2-Pole Power Distribution Block

By Burndy

Catalog # [BDBLHC1123502](#)



General

Catalog Number	BDBLHC1123502
Insulation	Y
Material	Aluminum
Number Of Poles	2
Plated	Y
Plating Type	Tin
Temperature Rating	194° F
Trade Name	VERSIPOLE™
UPC	781810645673
UPC 12 Digit	7818106456733

Dimensions

Dimension - Height inch	3.55
Dimension - Height mm	90.2 mm
Dimension - L Length Overall mm	135
Dimension - Length Overall inch	5.73
Dimension - Width inch	5.70 in
Dimension - Width mm	145 mm

Electrical Ratings

Amperage Rating	310 A
Rating - Minimum Voltage	600

Conductor Related

Conductor - AL Str Run	6;4;3;2;1;1/0;2/0;3/0;4/0;250;266.8;300;336;4;350
Conductor - AL Str Run Range	6-350
Conductor - AL Str Tap	12;10;8;6;4
Conductor - AL Str Tap Range	12-4
Conductor - Copper Str Run	6;5;4;3;2;1;1/0;2/0;3/0;4/0;250;300;350

Conductor - Copper Str Run Range	6-350
Conductor - Copper Str Tap	14;12;10;9;8;7;6;5;4
Conductor - Copper Str Tap Range	14-4
Conductor Type	<ul style="list-style-type: none"> • AL C Str-Run • CU C Str-Run • AL C Str-Tap • CU C Str-Tap

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	9
Minimum Pack Quantity	1

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_VERSIPOLE_Large_Lineart](#)
- [Sales Drawings - 50018991](#)
- [Specifications - BDBLHC1123502](#)