



# BDBSCS1C1FS, 1-Pole Flex Rated Finger-Safe Power Distribution Block

By Burndy  
Catalog # [BDBSCS1C1FS](#)

Distribution block, One pole Finger Safe 14-2/0 AWG (Run), 14-4 AWG (Tap).



## Features

- AL9CU dual rated for use with copper and aluminum conductors
- Range taking designs accommodate wire sizes up to 535 DLO and can support 1 or 2 run conductors and up to 12 taps for secondary circuits
- Allow for panel mounting, medium and large sizes also allow for DIN rail mounting
- Finger-Safe style are provided with translucent polycarbonate top covers and end plates permitting easy visual inspection, provide IEC 605219 IP-20 Rating
- Base and side barriers of glass-reinforced nylon 6/6 for extra durability and excellent insulating properties
- UL94 flammability rating of VO

## Application

VERSI-POLE Power Distribution Blocks are designed to provide modular solutions to power distribution applications.

## General

Connector Type	Power Distribution Block
EU RoHS Indicator	Yes
Insulation	Y
Material	Aluminum
Plated	Y
Plating Type	Tin
Sub Brand	VERSIPOLE
Temperature Rating	194
Trade Name	VERSIPOLE™
Type	BDB
UPC	781810676479
UPC 12 Digit	7818106764799

## Electrical Ratings

Rating - Minimum Voltage	600
Voltage - Maximum	600 V

## Conductor Related

Conductor Type	<ul style="list-style-type: none"><li>• AL C Str-Run</li><li>• CU C Str-Run</li><li>• AL C Str-Tap</li><li>• CU C Str-Tap</li></ul>
----------------	---

## Certifications And Compliance

Certification - CSA Approved	No
Certification - cULus	Yes
Standards - RoHS Compliance Status	CM

## Logistics

Carton Quantity	1
Minimum Pack Quantity	1

## Product Assets

[Catalogs - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Sales Drawings - 50059697](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
BRDY-BDBSCS1C1FS-SPEC-EN | REV 5/2024