

BDBMCS1F2, 2-Pole Flex Rated Power Distribution Block

By Burndy

Catalog # [BDBMCS1F2](#)

Distribution block, Two pole Open Style 14-2/0 AWG (Run), 14-2 AWG (Tap), Hole layout-1(Run)/6(Tap).



Application

VERSI-POLE Power Distribution Blocks are designed to provide modular solutions to power distribution applications.

General

Catalog Number	BDBMCS1F2
Connector Type	Power Distribution Block
EU RoHS Indicator	Yes
Insulation	Y
Material	Aluminum
Plated	Y
Plating Type	Tin
Sub Brand	VERSIPOLE
Temperature Rating	194
Trade Name	VERSIPOLE™
Type	BDB
UPC	781810676097
UPC 12 Digit	7818106760977

Dimensions

Dimension - Height mm	0 mm
-----------------------	------

Electrical Ratings

Rating - Minimum Voltage	600
Voltage - Maximum	600 V

Conductor Related

Conductor Type	<ul style="list-style-type: none"> AL C Str-Run CU C Str-Run AL C Str-Tap CU C Str-Tap
----------------	--

Certifications And Compliance

Buy American Compliant	Yes
Certification - CSA Approved	No
Certification - cULus	Yes
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	4
Minimum Pack Quantity	1
Pallet Quantity	384

Product Assets

- [Catalogs - BURNDY Master Catalog - Section A - Mechanical](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 50059696](#)
- [Specifications - BDBMCS1F2](#)