

BDBMCS2F1FS, 1-Pole Flex Rated Finger-Safe Power Distribution Block

By Burndy
Catalog # [BDBMCS2F1FS](#)



Distribution block, One pole Finger Safe 14-2/0 AWG (Run), 14-2 AWG (Tap), Hole layout- 2(Run)/6(Tap).

Application

VERSI-POLE Power Distribution Blocks are designed to provide modular solutions to power distribution applications.

General

Catalog Number	BDBMCS2F1FS
Connector Type	Power Distribution Block
EU RoHS Indicator	Yes
Insulation	Y
Material	Aluminum
Plated	Y
Plating Type	Tin
Sub Brand	VERSIPOLE
Temperature Rating	194
Trade Name	VERSIPOLE™
Type	BDB
UPC	781810676363
UPC 12 Digit	7818106763633

Dimensions

Dimension - Height mm	0 mm
Height	4.52 in
Length	5.71 in

Electrical Ratings

Rating - Minimum Voltage	600
--------------------------	-----

Voltage - Maximum	600 V
-------------------	-------

Conductor Related

Conductor Type	<ul style="list-style-type: none"> • AL C Str-Run • CU C Str-Run • AL C Str-Tap • CU C Str-Tap
----------------	--

Certifications And Compliance

Buy American Compliant	Yes
Certification - CSA Approved	No
Certification - cULus	Yes
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	1
Minimum Pack Quantity	1
Pallet Quantity	1215

Product Assets

- [Catalogs - BURNDY Master Catalog - Section A - Mechanical](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 50081547](#)
- [Specifications - BDBMCS2F1FS](#)