



## BDCSHC112/01, 1-Pole Power Distribution Block

By Burndy  
Catalog # BDCSHC112/01

Versipole, AWG 14-2/0 (Run), AWG 14-2/0 (Tap).



### Application

VERSI-POLE Power Distribution Blocks are designed to provide modular solutions to power distribution applications.

### General

Catalog Number	BDCSHC112/01
EU RoHS Indicator	Yes
Insulation	Y
Material	Aluminum
Number Of Poles	1
Plated	N
Plating Type	Unplated
Sub Brand	VERSI-POLE
Temperature Rating	194
Trade Name	VERSIPOLE™
Type	BDC
UPC	781810646151
UPC 12 Digit	7818106461511

### Dimensions

Dimension - Height inch	2.81 in
Dimension - L Length Overall mm	78 mm
Dimension - Length Overall inch	3.08 in
Dimension - Width inch	1.05 in
Dimension - Width mm	27 mm

### Electrical Ratings

Amperage Rating	175 A
Rating - Minimum Voltage	600

### Conductor Related

Conductor - AL Str Run	12;10;8;6;4;3;2;1;1/0;2/0
Conductor - AL Str Run Range	12-2/0
Conductor - AL Str Tap	12;10;8;6;4;3;2;1;1/0;2/0
Conductor - AL Str Tap Range	12-2/0
Conductor - Copper Str Run	14;12;10;9;8;7;6;5;4;3;2;1;1/0;2/0
Conductor - Copper Str Run Range	14-2/0
Conductor - Copper Str Tap	14;12;10;9;8;7;6;5;4;3;2;1;1/0;2/0
Conductor - Copper Str Tap Range	14-2/0
Conductor Type	<ul style="list-style-type: none"><li>AL C Str-Run</li><li>CU C Str-Run</li><li>AL C Str-Tap</li><li>CU C Str-Tap</li></ul>

### Certifications And Compliance

Buy American Compliant	Under Review
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

### Logistics

Carton Quantity	36
Minimum Pack Quantity	1

### Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Product Cross Section Image\(s\) - BUR\\_VERSIPOLE\\_Small\\_Lineart](#)  
[Sales Drawings - 50018987](#)  
[Specifications - BURNDY\\_BDCSHC11201\\_Specsheet](#)  
[Specifications - BDCSHC112/01](#)



A Hubbell brand