



BDCSHC142/01, 1-Pole Power Distribution Block

By Burndy
Catalog # [BDCSHC142/01](#)

Versipole, AWG 14-2/0 (Run), AWG 14-4 (Tap).



Application

VERSI-POLE Power Distribution Blocks are designed to provide modular solutions to power distribution applications.

General

Catalog Number	BDCSHC142/01
EU RoHS Indicator	Yes
Insulation	Y
Material	Aluminum
Number Of Poles	1
Plated	N
Plating Type	Unplated
Sub Brand	VERSI-POLE
Temperature Rating	194
Trade Name	VERSIPOLE™
Type	BDC
UPC	781810646168
UPC 12 Digit	7818106461688

Dimensions

Dimension - Height inch	2.81 in
Dimension - L Length Overall mm	78 mm
Dimension - Length Overall inch	3.08 in
Dimension - Width inch	1.05 in
Dimension - Width mm	27 mm

Electrical Ratings

Amperage Rating	175 A
Rating - Minimum Voltage	600

Conductor Related

Conductor - AL Str Run	12;10;8;6;4;3;2;1;1/0;2/0
Conductor - AL Str Run Range	12-2/0
Conductor - AL Str Tap	12;10;8;6;4
Conductor - AL Str Tap Range	12-4
Conductor - Copper Str Run	14;12;10;9;8;7;6;5;4;3;2;1;1/0;2/0
Conductor - Copper Str Run Range	14-2/0
Conductor - Copper Str Tap	14;12;10;9;8;7;6;5;4
Conductor - Copper Str Tap Range	14-4
Conductor Type	<ul style="list-style-type: none">AL C Str-RunCU C Str-RunAL C Str-TapCU C Str-Tap

Certifications And Compliance

Buy American Compliant	No
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	36
Minimum Pack Quantity	1

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_VERSIPOLE_Small_Lineart](#)
[Sales Drawings - 50018987](#)
[Specifications - Burndy_BDCSHC14201_Specsheet](#)
[Specifications - BDCSHC142/01](#)



A Hubbell brand