



## BDBMCS3SF1, Flex Rated Stud Style Power Distribution Block

By Burndy  
Catalog # BDBMCS3SF1

Power Distribution Block, Medium size, 1-Pole, Box-to-Stud Style, 3/8" stud Run Side, (4) #14 - 2/0 Tap Side, 350 Amp Rating.

### Features

- 600 Volt Rated
- Listed to UL1953
- Rated for use with code and flex conductor without requiring ferrules
- AL9CU dual rated for use with copper and aluminum conductors
- Range taking conductor ports can accommodate wire sizes up to 535 DLO and can support up to 5 run conductors and up to 24 tap conductors
- High Short-Circuit Current Rating up to 100kA with proper fusing

### General

Catalog Number	BDBMCS3SF1
Connector Type	Power Distribution Block
Material	Aluminum
UPC	621945481695

### Dimensions

Image represents single pole



Height	4.52 in
Length	5.71 in

### Certifications And Compliance

Certification - CSA Approved	No
Certification - cULus	Yes
Standards - RoHS Compliance Status	CM

### Logistics

Carton Quantity	1
Minimum Pack Quantity	1
Pallet Quantity	1215

### Product Assets

- [Catalogs - BURNDY Master Catalog - Section A - Mechanical](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 50081547](#)
- [Specifications - BDBMCS3SF1](#)