



BDBMCS3SM1, Flex Rated Stud Style Power Distribution Block

By Burndy

Catalog # [BDBMCS3SM1](#)

Power Distribution Block, Medium size, 1-Pole, Box-to-Stud Style, 3/8" stud Run Side, (4) #14 - 2/0 Tap Side, 350 Amp Rating.

Features

- 600 Volt Rated
- Listed to UL1953
- Rated for use with code and flex conductor without requiring ferrules
- AL9CU dual rated for use with copper and aluminum conductors
- Range taking conductor ports can accommodate wire sizes up to 535 DLO and can support up to 5 run conductors and up to 24 tap conductors
- High Short-Circuit Current Rating up to 100kA with proper fusing

General

Catalog Number	BDBMCS3SM1
Connector Type	Power Distribution Block
Material	Aluminum
UPC	621945481688

Dimensions

Image represents single pole



Height	4.52 in
Length	5.71 in

Certifications And Compliance

Certification - CSA Approved	No
Certification - cULus	Yes
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	1
Minimum Pack Quantity	1
Pallet Quantity	1215

Product Assets

- [Catalogs - BURNDY Master Catalog - Section A - Mechanical](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 50081547](#)
- [Specifications - BDBMCS3SM1](#)



A Hubbell brand