

BDBMCS3U3, 3-Pole Flex Rated Power Distribution Block

By Burndy
Catalog # [BDBMCS3U3](#)

Distribution block, Three pole Open Style 6 AWG- 350 Kcmil (Run), 6 AWG- 350 Kcmil (Tap).



Application

VERSI-POLE Power Distribution Blocks are designed to provide modular solutions to power distribution applications.

General

Catalog Number	BDBMCS3U3
Connector Type	Power Distribution Block
EU RoHS Indicator	Yes
Insulation	Y
Material	Aluminum
Plated	Y
Plating Type	Tin
Sub Brand	VERSIPOLE
Temperature Rating	194
Trade Name	VERSIPOLE™
Type	BDB
UPC	781810676318
UPC 12 Digit	7818106763188

Dimensions

Dimension - Height mm	0 mm
-----------------------	------

Electrical Ratings

Rating - Minimum Voltage	600
Voltage - Maximum	600 V

Conductor Related

Conductor Type	<ul style="list-style-type: none">AL C Str-RunCU C Str-RunAL C Str-TapCU C Str-Tap
----------------	---

Certifications And Compliance

Buy American Compliant	Contact Manufacturer
Certification - CSA Approved	No
Certification - cULus	Yes
Standards - RoHS Compliance	CM
Status	

Logistics

Carton Quantity	4
Minimum Pack Quantity	1
Pallet Quantity	384

Product Assets

[Catalogs - BURNDY Master Catalog - Section A - Mechanical](#)
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - 50059696](#)
[Specifications - BDBMCS3U3](#)