

BDBMHC112/03, 3-Pole Power Distribution Block

By Burndy
Catalog # BDBMHC112/03



Power Distribution Block, Glass Filled Polycarbonate, AWG 14 - 2/0 (Run), AWG 14 - 2/0 (Tap)

Application

Industrial control feeder, HVAC system and wire ways

General

Catalog Number	BDBMHC112/03
EU RoHS Indicator	Yes
Insulation	Y
Material	Aluminum
Number Of Poles	3
Plated	Y
Plating Type	Tin
Sub Brand	VERSI-POLE
Temperature Rating	194
Trade Name	VERSIPOLE™
Type	BDB
UPC	781810645659
UPC 12 Digit	7818106456599

Dimensions

Dimension - Height inch	3.25 in
Dimension - Height mm	82.6 mm
Dimension - L Length Overall mm	127 mm
Dimension - Length Overall inch	5.00 in
Dimension - Width inch	5.28 in
Dimension - Width mm	134 mm

Electrical Ratings

Amperage Rating	175 A
Rating - Minimum Voltage	600

Conductor Related

Conductor - AL Str Run	12;10;8;6;4;3;2;1;1/0;2/0
Conductor - AL Str Run Range	12-2/0
Conductor - AL Str Tap	12;10;8;6;4;3;2;1;1/0;2/0

Conductor - AL Str Tap Range	12-2/0
Conductor - Copper Str Run	14;12;10;9;8;7;6;5;4;3;2;1;1/0;2/0
Conductor - Copper Str Run Range	14-2/0
Conductor - Copper Str Tap	14;12;10;9;8;7;6;5;4;3;2;1;1/0;2/0
Conductor - Copper Str Tap Range	14-2/0
Conductor Type	<ul style="list-style-type: none"> • AL C Str-Run • CU C Str-Run • AL C Str-Tap • CU C Str-Tap

Certifications And Compliance

Buy American Compliant	No
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	6
Minimum Pack Quantity	1

Product Assets

- [3D Models - BDBMHC11203_MODEL-PDF](#)
- [3D Models - BDBMHC11203_MODEL-IGES](#)
- [3D Models - BDBMHC11203_MODEL-STEP](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_VERSIPOLE_Medium_Lineart](#)
- [Sales Drawings - 50018989](#)
- [Specifications - BDBMHC112/03](#)
- [Specifications - BURNDY_BDBMHC11203_Specsheet](#)