

BDBMHC162/03, 3-Pole Power Distribution Block

By Burndy
Catalog # BDBMHC162/03



POWER DISTRIBUTION BLOCKS.

General

| | |
|--------------------|---------------|
| Catalog Number | BDBMHC162/03 |
| Insulation | Y |
| Material | Aluminum |
| Number Of Poles | 3 |
| Plated | Y |
| Plating Type | Tin |
| Temperature Rating | 194 |
| Trade Name | VERSIPOLE™ |
| UPC | 781810645802 |
| UPC 12 Digit | 7818106458022 |

Dimensions

| | |
|---------------------------------|---------|
| Dimension - Height inch | 3.25 in |
| Dimension - Height mm | 82.6 mm |
| Dimension - L Length Overall mm | 127 mm |
| Dimension - Length Overall inch | 5.00 in |
| Dimension - Width inch | 5.28 in |
| Dimension - Width mm | 134 mm |

Electrical Ratings

| | |
|--------------------------|-------|
| Amperage Rating | 175 A |
| Rating - Minimum Voltage | 600 |

Conductor Related

| | |
|----------------------------------|------------------------------------|
| Conductor - AL Str Run | 12;10;8;6;4;3;2;1;1/0;2/0 |
| Conductor - AL Str Run Range | 12-2/0 |
| Conductor - AL Str Tap | 12;10;8;6;4;3;2 |
| Conductor - AL Str Tap Range | 12-2 |
| Conductor - Copper Str Run | 14;12;10;9;8;7;6;5;4;3;2;1;1/0;2/0 |
| Conductor - Copper Str Run Range | 14-2/0 |

| | |
|----------------------------------|--|
| Conductor - Copper Str Tap | 14;12;10;9;8;7;6;5;4;3;2 |
| Conductor - Copper Str Tap Range | 14-2 |
| Conductor Type | <ul style="list-style-type: none"> AL C Str-Run CU C Str-Run AL C Str-Tap CU C Str-Tap |

Certifications And Compliance

| | |
|------------------------------------|-----|
| Certification - CSA Approved | No |
| Certification - ETL | No |
| Certification - UL Recognized | No |
| Certification - cULus | No |
| Standards - RoHS Compliance Status | CM |
| UL Listed | Yes |

Logistics

| | |
|-----------------------|---|
| Carton Quantity | 6 |
| Minimum Pack Quantity | 1 |

Product Assets

- [3D Models - BDBMHC16203_MODEL-PDF](#)
- [3D Models - BDBMHC16203_MODEL-IGES](#)
- [3D Models - BDBMHC16203_MODEL-STEP](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_VERSIPOLE_Medium_Lineart](#)
- [Sales Drawings - 50018989](#)
- [Specifications - BDBMHC162/03](#)
- [Specifications - BURNDY_BDBMHC16203_Specsheet](#)