



## BDBSCS1S1S2, Flex Rated Stud Style Power Distribution Block

By Burndy

Catalog # [BDBSCS1S1S2](#)

POWER DISTRIBUTION BLOCK, 2 POLE 600V AL9CU, RUN:(1)  
1/4 STUD TAP:(1) 1/4 STUD.

### Features

- AL9CU dual rated for use with copper and aluminum conductors
- Range taking designs accommodate wire sizes up to 535 DLO and can support 1 or 2 run conductors and up to 12 taps for secondary circuits
- Allow for panel mounting, medium and large sizes also allow for DIN rail mounting
- Finger-Safe style are provided with translucent polycarbonate top covers and end plates permitting easy visual inspection, provide IEC 605219 IP-20 Rating
- Base and side barriers of glass-reinforced nylon 6/6 for extra durability and excellent insulating properties
- UL94 flammability rating of VO

### General

Catalog Number	BDBSCS1S1S2
Connector Type	Power Distribution Block
Material	Aluminum
Trade Name	VERSIPOLE™

Image represents single pole



UPC

621945518605

### Dimensions

Weight .36 lb

### Certifications And Compliance

Certification - CSA Approved	No
Certification - UL Recognized	No
Certification - cULus	Yes
Standards - RoHS Compliance Status	CM

### Logistics

Minimum Pack Quantity 1

### Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Specifications - BDBSCS1S1S2](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
BRDY-BDBSCS1S1S2-SPEC-EN | REV 10/2024