

# BIBS25010MT, Single Sided Mounted Ten Conductor Clear Insulated Mult-Tap Connector



By Burndy  
Catalog # [BIBS25010MT](#)

Aluminum Multiple Tap Connector w/ Mount Holes, Clear Insulated, 10 Port, 1 Sided Entry, 10 AWG-250 kcmil, Al/Cu Rated.

## Features

- Clear Plastisol covered AL6061-T6 aluminum body saves times and lowers installation costs and eliminates taping
- Clear plastisol allows visual confirmation that conductor is properly inserted
- Oxide inhibitor pre-installed inhibits moisture and contaminants from entering the contact area
- Range-taking capability reduces number of connectors necessary to carry in inventory

## General

Catalog Number	BIBS25010MT
Connector Type	Multi Tap
Hex Key	5/16
Insulation	Y
Insulation Type	Plastisol
Material	Aluminum
Number Of Ports	10
Physical Attribute - Number of Screws	12
Physical Attribute - Screw Type	Allen
Plated	N
Plating Type	Unplated
Temperature Rating	194
Trade Name	UNITAP™
UPC	781810252956
UPC 12 Digit	7818102529566

## Dimensions

Dimension - Height inch	2.63 in
Dimension - Height mm	67 mm
Dimension - L Length Overall mm	290 mm
Dimension - Length Overall inch	11.41 in
Dimension - Width inch	1.95 in
Dimension - Width mm	50 mm

## Electrical Ratings

Operating Voltage	600 V
Voltage - Maximum	600 V

## Conductor Related

Conductor - AL Str Size Range	10 AWG - 250 kcmil
Conductor - Copper Str Size Range	10 AWG - 250 kcmil
Conductor Size	10 AWG-250 KCMIL
Conductor Type	<ul style="list-style-type: none"> <li>• AL C Str-Size</li> <li>• CU C Str-Size</li> </ul>

## Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Listed Direct Burial	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Minimum Pack Quantity	5
-----------------------	---

## Product Assets

- [Catalogs - UNITAP™ Products](#)
- [Catalogs - BURNDY Master Catalog - Section A - Mechanical](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR\\_BIBS-MT\\_LineArt](#)
- [Sales Drawings - 213079](#)
- [Specifications - BIBS25010MT](#)



A Hubbell brand

©2025 Hubbell Incorporated. All rights reserved  
BRDY-BIBS25010MT-SPEC-EN | REV 1/2025