



BIPC1/08SC, Insulation Piercing Connector for Cu/Al, Run: #8-1/0, Tap: #8-1/0

By Burndy
Catalog # [BIPC1/08SC](#)

Insulation Piercing Connector for Copper and Aluminum, Run: #8-1/0, Tap: #8-1/0, ideal for splicing, tapping and dead-ending aluminum and copper conductor with shearing installation technology. 6-point socket impact driver for easy installation and removal, no torque wrench required.

Features

- Flexibility! One connector allows for tap, splice or dead-end configurations
- Time Savings! Requires no cable stripping, conductor brushing, inhibitor application or after installation taping
- Engineered shear bolt technology applies consistent torque for efficient and reliable connectors
- Easy installation and removal - only requires 6-point socket impact driver
- cULus Listed Splicing Wire Connector, AL9CU Rated, for copper and aluminum conductor combinations up to 90 degrees C, *600 Volt applications
- Insulation piercing design for use in multiple applications - overhead covered and bare taps, service and metering connections, and lighting system work



General

Application - For Use On	Copper and Aluminum
Catalog Number	BIPC1/08SC
UPC	621945652989

Logistics

Carton Quantity	12
Pallet Quantity	1080

Product Assets

[Catalogs - BURNDY Master Catalog - Section A - Mechanical](#)
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Specifications - BIPC1/08SC](#)