

## BFB624T12 Flexible Bus Bar Lug Terminal

By Burndy  
Catalog # [BFB624T12](#)



Industry-exclusive Compression Solution for flexible Bus Bar Applications.

### Features

- Industry Exclusive! Only offered by BURNDY®
- Eliminates the need to drill through copper sheets, ensuring a cleaner, faster installation
- Full inspectability with the BURNDY® Engineered System
- 1-hole and 2-hole options available to accommodate spacing requirements
- Most flexible bus bar sizes accommodated
- Locator lines on terminals provide for accurate and consistent crimping
- UL Recognized to UL67 for Panelboard Equipment

### Application

Typically used in panelboards, switchboards, transformers, control panels, and similar applications

### General

Catalog Number	BFB624T12
Number of Holes	1
UPC	621945531741

### Dimensions

Dimension - Stud Size inch	1/2 in
Length	2.75 in

### Logistics

Carton Quantity	40
Minimum Pack Quantity	1
Pallet Quantity	18560

### Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Catalogs - BURNDY Master Catalog - Section E1 - Compression Grounding](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Sales Drawings - 50077538](#)  
[Specifications - BFB624T12](#)