



Insulation Piercing Connector for Cu/Al, Run: #8-1/0, Tap: #10-#2

By Burndy
Catalog # [BIPC1/010SC](#)

Insulation Piercing Connector for Copper and Aluminum, Run: #8-1/0, Tap: #10-#2, ideal for splicing, tapping and dead-ending aluminum and copper conductor with shearing installation technology. 6-point socket impact driver for easy installation and removal, no torque wrench required.



Features

- Flexibility! One connector allows for tap, splice or dead-end configurations
- Time Savings! Requires no cable stripping, conductor brushing, inhibitor application or after installation taping
- Engineered shear bolt technology applies consistent torque for efficient and reliable connectors
- Easy installation and removal - only requires 6-point socket impact driver
- cULus Listed Splicing Wire Connector, AL9CU Rated, for copper and aluminum conductor combinations up to 90 degrees C, *600 Volt applications
- Insulation piercing design for use in multiple applications - overhead covered and bare taps, service and metering connections, and lighting system work

Application

Insulation Piercing Connector

General

Application - For Use On Copper and Aluminum
UPC 621945652972

Logistics

Carton Quantity 12
Pallet Quantity 1080

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-BIPC1/010SC-SPEC-EN | REV 1/2024