

BGBL1/0, Aluminum Lay-in Lug, 1/0-14 AWG, 3/8" Stud, Tin Plated

By Burndy
Catalog # BGBL1/0



Aluminum Lay-in Lug, 1/0-14 AWG, 3/8" Stud, Tin Plated.

Features

- UL486B Listed, AL9CU Rated for copper and aluminum conductor combinations up to 90°C, 600 Volt applications
- UL Recognized for grounding and bonding
- Lay-in feature eases installation

Application

For Copper And Aluminum Conductor Combinations Up To 90 DEG C

General

Catalog Number	BGBL1/0
EU RoHS Indicator	Yes
Hex Size	Slot
Installation Torque	50 LBS/in
Recommended in-lb	
Material	Aluminum
Material Type - Screw	Steel - Zinc Plated
Physical Attribute - Screw Type	Slot
Plated	Y
Plating Type	Tin
Sub Brand	QIKLUG
Temperature Rating	194
Trade Name	QIKLUG™
Type	BGBL, Lay-In
UPC	781810124840
UPC 12 Digit	7818101248400

Dimensions

Dimension - D inch	0.80 in
Dimension - Height fraction	1-1/6 in
Dimension - Height inch	1.17 in
Dimension - Hole Size inch	0.28 in
Dimension - Hole Size mm	7 mm
Dimension - L Length Overall mm	38 mm
Dimension - Length Overall inch	1.50 in
Dimension - N inch	0.3 in
Dimension - Pad Width inch	0.60 in

Conductor Related

Conductor - AL Str Size	8 AWG;6 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 AWG
Conductor - AL Str Size Range	8 AWG-1/0 AWG
Conductor - Copper Solid Size	14 AWG;13 AWG;12 AWG;11 AWG;10 AWG;9 AWG;8 AWG;7 AWG;6 AWG;5 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 AWG
Conductor - Copper Solid Size Range	14 AWG-1/0 AWG
Conductor - Copper Str Size	14 AWG;12 AWG;10 AWG;9 AWG;8 AWG;7 AWG;6 AWG;5 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0
Conductor - Copper Str Size Range	14 AWG - 1/0 AWG
Conductor Type	<ul style="list-style-type: none"> • AL C Str-Size • CU C Str-Size • CU C Solid-Size

Certifications And Compliance

Buy American Compliant	Yes
Certification - CSA Approved	Yes
Certification - UL Listed Direct Burial	No
Industry Standard(s)	UL 486A-B
Standards - Industry Standards Met	UL 486A-B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	600
Minimum Pack Quantity	1

Product Assets

[3D Models - BGBL10_MODEL-STEP](#)

[3D Models - BGBL10_MODEL-PDF](#)

[3D Models - BGBL10_MODEL-IGES](#)

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)

[Catalogs - BURNDY Master Catalog - Section A - Mechanical](#)

[Customer Notices - Prop 65 Notice](#)

[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)

[Product Cross Section Image\(s\) - BUR_BGBL_LineArt](#)

[Sales Drawings - SE..212385-01](#)

[Specifications - BGBL1/0](#)

[Specifications - Burndy_BGBL10_Specsheet](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRDY-BGBL10-SPEC-EN | REV 8/2024