



# BGBL4, Aluminum Lay-in Lug, 4-14 AWG, 1/4" Stud, Tin Plated

By Burndy  
Catalog # BGBL4



Aluminum Lay-in Lug, 4-14 AWG, 1/4" Stud, Tin Plated.

## Application

For Copper And Aluminum Conductor Combinations Up To 90 DEG C, 600 Volt Applications

## General

EU RoHS Indicator	Yes
Hex Size	Slot
Installation Torque Recommended in-lb	35 LBS/in
Material	Aluminum
Material Type - Screw	Steel - Zinc Plated
Physical Attribute - Screw Type	Slot
Plated	Y
Plating Type	Tin
Sub Brand	QIKLUG
Temperature Rating	194
Trade Name	QIKLUG™
Type	BGBL, Lay-In
UPC	781810124857
UPC 12 Digit	7818101248577

## Dimensions

Dimension - D inch	0.62 in
Dimension - Height fraction	7/9 in
Dimension - Height inch	0.78 in
Dimension - Hole Size inch	0.22 in
Dimension - Hole Size mm	6 mm
Dimension - L Length Overall mm	27 mm
Dimension - Length Overall inch	1.07 in
Dimension - N inch	0.19 in
Dimension - Pad Width inch	0.38 in

## Electrical Ratings

Voltage - Maximum	600 V
-------------------	-------

## Conductor Related

Conductor - AL Str Size	8 AWG;6 AWG;4 AWG
Conductor - AL Str Size Range	8 AWG-4 AWG
Conductor - Copper Solid Size	14 AWG;13 AWG;12 AWG;11 AWG;10 AWG;9 AWG;8 AWG;7 AWG;6 AWG;5 AWG;4 AWG
Conductor - Copper Solid Size Range	14 AWG-4 AWG
Conductor - Copper Str Size	14 AWG;12 AWG;10 AWG;9 AWG;8 AWG;7 AWG;6 AWG;5 AWG;4 AWG
Conductor - Copper Str Size Range	14 AWG-4 AWG
Conductor Type	<ul style="list-style-type: none"><li>AL C Str-Size</li><li>CU C Str-Size</li><li>CU C Solid-Size</li></ul>

## Certifications and Compliance

Certification - CSA Approved	Yes
Industry Standard(s)	UL 486A-B
Standards - Industry Standards Met	UL 486A-B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Carton Quantity	2400
Minimum Pack Quantity	1

## Product Assets

[3D Models - BGBL4\\_MODEL-STEP](#)  
[3D Models - BGBL4\\_MODEL-PDF](#)  
[3D Models - BGBL4\\_MODEL-IGES](#)  
[Catalogs - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Sales Drawings - SE..212385-01](#)



A proud member of the Hubbell Family.

