

# BIBD2503FX, Double Sided Flex Rated Three Conductor Clear Insulated Mult-Tap Connector



By Burndy  
Catalog # [BIBD2503FX](#)

Aluminum UNITAP, Double Sided Entry, #10-250 Class B & C, #10-3/0 Class G,H,I,K, DLO, 3 PORT

## Features

- Clear Plastisol covered AL6061-T6 aluminum body saves times and lowers installation costs and eliminates taping
- Clear plastisol allows visual confirmation that conductor is properly inserted
- Oxide inhibitor pre-installed inhibits moisture and contaminants from entering the contact area
- Range-taking capability reduces number of connectors necessary to carry in inventory
- Suitable for Code and Flex Conductor
- Color-coordinated conductor port caps display wire range and classes of conductor accepted
- Screw port caps show installation torque information for easy reference

## Application

Tap connections and in-line splice/reductions are made quickly and easily with the UNITAP™ line of connectors

## General

Catalog Number	BIBD2503FX
Connector Type	Multi Tap
EU RoHS Indicator	Yes
Insulation	Y
Material	Aluminum
Plated	N
Plating Type	Unplated
Sub Brand	UNITAP
Temperature Rating	194
Trade Name	UNITAP™
Type	BIBD, Multi-Port
UPC	621945438996
UPC 12 Digit	6219454389966

## Dimensions

Dimension - Height mm 0 mm

## Electrical Ratings

Voltage - Maximum 600 V

## Conductor Related

Conductor Size 10 AWG-250 KCMIL  
Conductor Type

- AL C Str-Size
- CU C Str-Size

## Certifications And Compliance

Buy American Compliant	Under Review
Certification - CSA Approved	Yes
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Minimum Pack Quantity 1

## Product Assets

[Catalogs - UNITAP™ Products](#)  
[Catalogs - BURNDY Master Catalog - Section A - Mechanical](#)  
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Sales Drawings - 50046931](#)  
[Specifications - BIBD2503FX](#)