

BIBD44, Double Sided Four Conductor Clear Insulated Multi-Tap Connector

By Burndy
Catalog # [BIBD44](#)



Aluminum Multiple Tap Connector, Clear Insulated, 4 Port, 2 Sided Entry, 14-4 AWG, Al/Cu Rated.

Application

For Indoor Use Only, Copper Or Stranded Aluminum

General

Connector Type	Multi Tap
EU RoHS Indicator	Yes
Hex Key	1/8
Insulation	Y
Insulation Type	Plastisol
Material	Aluminum
Material - Hardware	Aluminum
Number Of Ports	4
Physical Attribute - Number of Screws	4
Physical Attribute - Screw Type	Allen
Plated	N
Plating Type	Unplated
Sub Brand	UNITAP
Temperature Rating	194
Trade Name	UNITAP™
Type	BIBD, Multi-Port
UPC	781810223864
UPC 12 Digit	7818102238644

Dimensions

Dimension - Height fraction	1.25 in
Dimension - Height inch	1.25 in
Dimension - L Length Overall mm	50 mm
Dimension - Length Overall inch	1.95 in
Dimension - Screw Size inch	1/4
Dimension - Width fraction	1-1/2 in
Dimension - Width inch	1.50 in
Dimension - Width mm	38 mm

Electrical Ratings

Voltage - Maximum	600 V
-------------------	-------

Conductor Related

Conductor - AL Str Size	8 AWG;6 AWG;4 AWG
Conductor - AL Str Size Range	8 AWG-4 AWG
Conductor - Copper Str Size	14 AWG;12 AWG;10 AWG;9 AWG;8 AWG;7 AWG;6 AWG;5 AWG;4 str
Conductor - Copper Str Size Range	14 AWG - 4 AWG
Conductor Size	14-4 AWG
Conductor Type	<ul style="list-style-type: none"> • AL C Str-Size • CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Listed Direct Burial	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[3D Models - BIBD44_MODEL-PDF](#)
[3D Models - BIBD44_MODEL-IGES](#)
[3D Models - BIBD44_MODEL-STEP](#)
[Catalogs - UNITAP™ Products](#)
[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - sc210991-04](#)

