

BITO600FX, Opposite Side Flex Rated Two Conductor Clear Insulated Multi-Tap Connector



By Burndy

Catalog # [BITO600FX](#)

Aluminum UNITAP, Tap - Opposite Side Entry, #4-600 Class B & C, #4-373 Class G,H,I,K, DLO, 2 PORT.

Features

- Type BIT-FX and BITO-FX Multi-tap connectors are quickly and easily installed
- UL486B Listed, Dual rated AL9CUFor stranded copper or stranded aluminum applications

General

Catalog Number	BITO600FX
Color Code	Green
Connector Type	Multi Tap
Hex Key	3/8 in
Insulation	Y
Material	Aluminum
Number Of Ports	2
Plated	Y
Plating Type	Tin Plated
Temperature Rating	135°C
Trade Name	UNITAP™
UPC	621945440685
UPC 12 Digit	6219454406855

Dimensions

Dimension - Height inch	2.75 in
Dimension - Height mm	69.85 mm
Dimension - L Length Overall mm	69.85 mm
Dimension - Length Overall inch	2.75 in
Dimension - Width inch	2.75 in
Dimension - Width mm	69.85 mm

Electrical Ratings

Operating Voltage	600 V
Voltage - Maximum	600 V

Conductor Related

Conductor - AL Str Size Range	4 AWG - 600 kcmil
Conductor - Copper DLO Size Range	4 str.-373 kcmil
Conductor - Copper Flex G Size Range	4 str.-373 kcmil
Conductor - Copper Flex H Size Range	4 str.-373 kcmil
Conductor - Copper Flex I Size Range	4 str.-373 kcmil
Conductor - Copper Flex K Size Range	4 str.-373 kcmil
Conductor - Copper Str Size Range	4 AWG - 600 kcmil
Conductor Size	4 AWG-600 KCMIL
Conductor Type	<ul style="list-style-type: none">• AL C Str-Size• CU C Str-Size• CU C Flex-Size

Certifications And Compliance

Certification - CSA Approved	Yes
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

- [Catalogs - UNITAP™ Products](#)
- [Catalogs - BURNDY Master Catalog - Section A - Mechanical](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 50046931](#)
- [Specifications - BITO600FX](#)