

BIBS2508, Single Sided Eight Conductor Clear Insulated Multi-Tap Connector

By Burndy
Catalog # [BIBS2508](#)



Aluminum Multiple Tap Connector, Clear Insulated, 8 Port, 1 Sided Entry, 10 AWG-250 kcmil, Al/Cu Rated.

Features

- Clear Plastisol covered AL6061-T6 aluminum body saves times and lowers installation costs and eliminates taping
- Clear plastisol allows visual confirmation that conductor is properly inserted
- Oxide inhibitor pre-installed inhibits moisture and contaminants from entering the contact area
- Range-taking capability reduces number of connectors necessary to carry in inventory

Application

For Indoor Use Only, Copper Or Stranded Aluminum

General

Catalog Number	BIBS2508
Connector Type	Multi Tap
EU RoHS Indicator	Yes
Hex Key	5/16
Insulation	Y
Insulation Type	Plastisol
Material	Aluminum
Number Of Ports	8
Physical Attribute - Number of Screws	8
Physical Attribute - Screw Type	Allen
Plated	N
Plating Type	Unplated
Sub Brand	UNITAP
Temperature Rating	194
Trade Name	UNITAP™
Type	BIBS, Multi-Port
UPC	781810131787
UPC 12 Digit	7818101317877

Dimensions

Dimension - Height inch	2.13 in
Dimension - Height mm	54 mm
Dimension - L Length Overall mm	195 mm
Dimension - Length Overall inch	7.66 in

Dimension - Width inch	2.07 in
Dimension - Width mm	53 mm

Electrical Ratings

Voltage - Maximum	600 V
-------------------	-------

Conductor Related

Conductor - AL Str Size Range	10 AWG - 250 kcmil
Conductor - Copper Str Size Range	10 AWG - 250 kcmil
Conductor Size	10 AWG-250 KCMIL
Conductor Type	<ul style="list-style-type: none"> • AL C Str-Size • CU C Str-Size

Certifications And Compliance

Buy American Compliant	Yes
Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Listed Direct Burial	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

- [3D Models - BIBS2508_MODEL-STEP](#)
- [3D Models - BIBS2508_MODEL-IGES](#)
- [3D Models - BIBS2508_MODEL-PDF](#)
- [Catalogs - BURNDY Master Catalog - Section A - Mechanical](#)
- [Catalogs - UNITAP™ Products](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)



A Hubbell brand