

# BIBS5005DB, Direct Burial Submersible Five Conductor Insulated Multi-Tap Connector



By Burndy  
Catalog # [BIBS5005DB](#)

Multi-Port Single Sided Entry, Multi-Port Single Sided Entry, 5,  
500 kcmil-12 AWG Str.

## Application

For Outside Direct Burial

## General

Catalog Number	BIBS5005DB
Connector Type	Multi Tap
EU RoHS Indicator	Yes
Installation Torque	550 LBS/in
Recommended in-lb	
Insulation	Y
Material	Aluminum
Number Of Ports	5
Plated	N
Plating Type	Unplated
Sub Brand	UNITAP
Temperature Rating	194
Trade Name	UNITAP™
Type	BIBS, Multi-Port - Direct Burial
UPC	781810523650
UPC 12 Digit	7818105236500

## Dimensions

Dimension - Height inch	3.13 in
Dimension - Height mm	80 mm
Dimension - L Length Overall mm	179 mm
Dimension - Length Overall inch	7.06 in
Dimension - Strip Length inch	1.5
Dimension - Width inch	4.58 in
Dimension - Width mm	116 mm

## Electrical Ratings

Operating Voltage	600 V
Voltage - Maximum	600 V

## Conductor Related

Conductor - AL Str Size Range	12 AWG - 500 kcmil
Conductor - Copper Str Size Range	12 AWG - 500 kcmil
Conductor Size	12 AWG-500 KCMIL
Conductor Type	<ul style="list-style-type: none"><li>AL C Str-Size</li><li>CU C Str-Size</li></ul>

## Certifications And Compliance

Buy American Compliant	Yes
Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes

## Logistics

Minimum Pack Quantity	1
-----------------------	---

## Product Assets

- [3D Models - BIBS5005DB\\_MODEL-STEP](#)
- [3D Models - BIBS5005DB\\_MODEL-IGES](#)
- [3D Models - BIBS5005DB\\_MODEL-PDF](#)
- [Catalogs - BURNDY Master Catalog - Section A - Mechanical](#)
- [Catalogs - UNITAP™ Products](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR\\_BIBS\\_Lineart](#)
- [Sales Drawings - 30013660](#)
- [Specifications - BIBS5005DB](#)