




## BTCGC250SS, Aluminum Ground Tray Clamp, #6-250 kcmil

By Burndy  
Catalog # [BTCGC250SS](#)

Aluminum ground tray clamp, accomodates ground wire size #6 to 250 Kcmil



### Features

- Tin plated aluminum for durable, long lasting corrosion resistance
- cULus 467 Listed for Grounding and Bonding in US and Canada
- cULus 2703 Listed for solar PV applications in US and Canada
- Accommodates most popular styles of cable tray with inside or outside flange
- Quick and easy installation
- no drilling or special tools required
- Set screw bonds clamp to the cable tray while another set screw securely fastens the grounding conductor to the clamp providing vibration resistance and outstanding pull-out values
- Grounding green hardware as required in Section 8.4 of UL2703

### Application

Type BTCGC-SS clamps are suitable for outdoor applications and may be used with most types of cable tray with an inside or outside flange design

### General

Allen Key Size	1/4 in
EU RoHS Indicator	Contact Manufacturer
Finish Type	Tin Plated
Material	Aluminum
Material - Hardware	Stainless steel
UPC	621945505957

### Dimensions

Dimensions	2.25 in x 0.88 in x 2.43 in
Height	2.43 in
Length	2.25 in
Thickness - Flange Plate	1/2 in
Width	0.88 in

### Conductor Related

Conductor - AL Str Size Range	#6 AWG - 250 Kcmil
Conductor - Copper Str Size Range	6 AWG - 250 kcmil
Conductor Range	#6 AWG - 250 Kcmil AL-CU

### Certifications And Compliance

Certified Listed	cULus Listed
------------------	--------------

### Product Assets

[Catalogs - Full Line BURNDY Catalog](#)  
[Sales Drawings - 50087187](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
BRDY-BTCGC250SS-SPEC-EN | REV 5/2024