

BYNA36RT15HHT, Compression Terminal Pad Assembly for ACSS 477 kcmil, includes Hardware, 15 Degree



By Burndy
Catalog # [BYNA36RT15HHT](#)

BURNDY; HYLUG; BYNA-RT-HHT, EHV; Features: Terminal and hardware; Full tension compression deadend for 250 Deg C rated ACSS transmission lines at 345 kV and over; 15 Deg NEMA Tap Pad Terminal; For ACSS Conductor; RoHS Compatible; Conductor Range (Main/Primary): 477 KCMIL ACSS.

General

Catalog Number	BYNA36RT15HHT
Connector Type	Terminal
Die Index	720
Feature - Barrel Style	Tapered
Feature - Barrel Type	Long
Material	Aluminum
Physical Attribute - Number of Holes	4
UPC	781810514184
UPC 12 Digit	7818105141844

Dimensions

Dimension - Bolt Size fraction	1/2
Dimension - D inch	4.5 in
Dimension - F Width Center to Center inch	1.75 in
Dimension - Hole Size inch	0.56 in
Dimension - Length Overall inch	16.76 in
Dimension - N inch	0.62 in
Dimension - Outside Diameter inch	1.41 in
Dimension - Pad Width inch	3.25 in
Dimension - Thread Size	1/2
Physical Attribute - Tongue Angle	15 Degree

Conductor Related

Conductor - ACSS Str Size	477 (20/7) kcmil;477 (22/7) kcmil;477 (24/7) kcmil;477 (26/7) kcmil;477 (30/7) kcmil
Conductor - ACSS Str Size Range	477 (20/7) kcmil-477 (30/7) kcmil

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 10092588](#)
- [Specifications - BYNA36RT15HHT](#)