



BYNA39RTHACCC, Terminal Pad Assembly, includes TMH24 Hardware Kit, 713 kcmil, 330mm, 380mm ACCC

By Burndy
Catalog # [BYNA39RTHACCC](#)



HYLUG™ Terminal Pad Assembly (ACCC) with TMH24 Hardware Kit, 713 kcmil, 330mm², 380mm² ACCC, 230kV.

General

Connector Type	Terminal
Die Index	722
Installation Torque Recommended in-lb	300 in-lb
Material	Aluminum
Trade Name	HYLUG™
UPC	781810506660
UPC 12 Digit	7818105066600

Dimensions

Dimension - D inch	4.50 in
Dimension - Hole Size inch	0.56 in
Dimension - Inside Diameter inch	0.97 in
Dimension - L Length Overall mm	411 mm
Dimension - Length Overall inch	16.2 in
Dimension - Outside Diameter inch	1.50 in
Dimension - Pad Width inch	3.25 in
Physical Attribute - Tongue Angle	Straight

Conductor Related

Conductor - ACCC Str Size	713 kcmil(Dove);330mm ² (Oslo);380mm ² (Amst)
---------------------------	---

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

- [3D Models - BYNA39RTHACCC_MODEL-STEP](#)
- [3D Models - BYNA39RTHACCC_MODEL-PDF](#)
- [3D Models - BYNA39RTHACCC_MODEL-IGES](#)
- [Catalogs - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Sales Drawings - 10093977](#)



A proud member of the Hubbell Family.