



BISR500, Clear Insulated Splice Reducer

By Burndy
Catalog # BISR500



Aluminum In-Line Splice, 6 AWG-500 kcmil.

Features

- Type BISR In-Line Splice/Reducers are easily installed on code conductor
- UL486B Listed, Dual rated AL9CU for any stranded copper or stranded aluminum applications

Application

For Indoor Use Only

General

Catalog Number	BISR500
Connector Type	In-Line
EU RoHS Indicator	Yes
Hex Key	5/16 in
Installation Torque	275 in-lb
Recommended in-lb	
Insulation	Y
Insulation Type	Plastisol
Material	Aluminum
Material - Hardware	Aluminum
Number Of Ports	2
Physical Attribute - Number of Screws	2
Physical Attribute - Screw Type	Allen
Plated	N
Plating Type	Unplated
Sub Brand	UNITAP
Temperature Rating	90 °C
Trade Name	UNITAP™
Type	BISR, In-Line
UPC	781810134085
UPC 12 Digit	7818101340855

Dimensions

Dimension - Height fraction	2.625 in
Dimension - Height inch	2.62 in
Dimension - L Length Overall mm	127 mm
Dimension - Length Overall inch	5 in
Dimension - Width fraction	1-31/50 in
Dimension - Width inch	1.62 in
Dimension - Width mm	41 mm

Electrical Ratings

Operating Voltage	600 V
Voltage - Maximum	600 V

Conductor Related

Conductor - AL Str Size	6 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 AWG;2/0 AWG;3/0 AWG;4/0 AWG;250 kcmil;266 kcmil;300 kcmil;336 kcmil;350 kcmil;397 kcmil;400 kcmil;450 kcmil;477 kcmil;500 kcmil
Conductor - AL Str Size Range	6 AWG - 500 kcmil
Conductor - Copper Str Size	#6;5 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 ;2/0 AWG;3/0 AWG;4/0 AWG;250 kcmil;300 kcmil;350 kcmil;400 kcmil;450 kcmil;500
Conductor - Copper Str Size Range	6 AWG - 500 kcmil
Conductor Size	6 AWG-500 KCMIL
Conductor Type	<ul style="list-style-type: none"> • AL C Str-Size • CU C Str-Size

Certifications And Compliance

Buy American Compliant	Yes
Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Listed Direct Burial	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[3D Models - BISR500_MODEL-PDF](#)

[3D Models - BISR500_MODEL-IGES](#)

[3D Models - BISR500_MODEL-STEP](#)

[Catalogs - BURNDY Master Catalog - Section A - Mechanical](#)

[Catalogs - UNITAP™ Products](#)

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)

[Customer Notices - Prop 65 Notice](#)

[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)

[Product Cross Section Image\(s\) - BUR_BISR_Lineart](#)

[Sales Drawings - sc210991-03](#)

[Specifications - BISR500](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRDY-BISR500-SPEC-EN | REV 8/2024