



BYNA43RTHACCC, Terminal Pad Assembly with TMH24 Hardware Kit, 816 kcmil-430mm ACCC, 230kV

By Burndy
Catalog # [BYNA43RTHACCC](#)



HYLUG™ Terminal Pad Assembly (ACCC) with TMH24 Hardware Kit, 816 kcmil-430mm² ACCC, 230kV.

General

Catalog Number	BYNA43RTHACCC
Connector Type	Terminal
Die Index	724
Installation Torque	300 in-lb
Recommended in-lb	
Material	Aluminum
Trade Name	HYLUG™
UPC	781810499368
UPC 12 Digit	7818104993688

Dimensions

Dimension - D inch	4.50 in
Dimension - Hole Size inch	0.56 in
Dimension - Inside Diameter inch	1.05 in
Dimension - L Length Overall mm	412 mm
Dimension - Length Overall inch	16.2 in
Dimension - Outside Diameter inch	1.61 in
Dimension - Pad Width inch	3.25 in
Physical Attribute - Tongue Angle	Straight

Conductor Related

Conductor - ACCC Str Size	816
	kcmil(Grosbeak);430mm ² (Brussels)
Conductor - ACCC Str Size Range	816
	kcmil(Grosbeak)-430mm ² (Brussels)

Certifications And Compliance

Standards - RoHS Compliance Status	UI
------------------------------------	----

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Catalogs - BURNDY Master Catalog - Section I - Transmission](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - 10093977](#)
[Specifications - BYNA43RTHACCC](#)