



# BYNA49RT15ACCC, Terminal Pad Assembly, 1222 kcmil, 650mm, 690mm, 710mm ACCC, 15 Degree, 230kv

By Burndy  
Catalog # [BYNA49RT15ACCC](#)



HYLUG™ Terminal Pad Assembly (ACCC), 1222 kcmil, 650mm<sup>2</sup>, 690mm<sup>2</sup>, 710mm<sup>2</sup> ACCC, 15°, 230kV.

## General

Connector Type	Terminal
Die Index	727
Feature - Barrel Style	Tapered
Installation Torque Recommended in-lb	300 in-lb
Material	Aluminum
Physical Attribute - Number of Holes	4
Trade Name	HYLUG™
UPC	781810514412
UPC 12 Digit	7818105144122

## Dimensions

Dimension - Bolt Size fraction	1/2
Dimension - D inch	3.95 in
Dimension - F Width Center to Center inch	1.75 in
Dimension - Hole Size inch	0.56 in
Dimension - Inside Diameter inch	1.32 in
Dimension - Length Overall inch	15.7 in
Dimension - N inch	0.63 in
Dimension - Outside Diameter inch	1.97 in
Dimension - Pad Width inch	3.22 in
Dimension - Thread Size	1/2
Physical Attribute - Tongue Angle	15 Degree

## Conductor Related

Conductor - ACCC Str Size	1222 kcmil(Cardinal);650mm <sup>2</sup> (Vienna);690mm <sup>2</sup> (Prague)
Conductor - ACCC Str Size Range	1222 kcmil(Cardinal)-710mm <sup>2</sup> (Prague)

## Certifications and Compliance

Standards - RoHS Compliance UI Status

## Logistics

Minimum Pack Quantity 1

## Product Assets

- [3D Models - BYNA49RT15ACCC\\_MODEL-STEP](#)
- [3D Models - BYNA49RT15ACCC\\_MODEL-IGES](#)
- [3D Models - BYNA49RT15ACCC\\_MODEL-PDF](#)
- [Catalogs - Full Line BURNDY Catalog](#)
- [Sales Drawings - 10093976](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
BRDY-BYNA49RT15ACCC-SPEC-EN | REV 1/2024