



# BYNA49RT15HACCC, Terminal Pad Assembly with TMH24 Hardware Kit, 1222 kcmil, 650mm, 690mm, 710mm ACCC, 15 Degree, 230kV



By Burndy  
Catalog # [BYNA49RT15HACCC](#)

HYLUG™ Terminal Pad Assembly (ACCC) with TMH24 Hardware Kit, 1222 kcmil, 650mm², 690mm², 710mm² ACCC, 15°, 230kV.

## General

Catalog Number	BYNA49RT15HACCC
Connector Type	Terminal
Die Index	727
Installation Torque Recommended in-lb	300 in-lb
Material	Aluminum
Trade Name	HYLUG™
UPC	781810474631
UPC 12 Digit	7818104746311

## Dimensions

Dimension - D inch	3.95 in
Dimension - Hole Size inch	0.56 in
Dimension - Inside Diameter inch	1.32 in
Dimension - L Length Overall mm	399 mm
Dimension - Length Overall inch	15.7 in
Dimension - Outside Diameter inch	1.97 in
Dimension - Pad Width inch	3.22 in
Physical Attribute - Tongue Angle	15 Degree

## Conductor Related

Conductor - ACCC Str Size	1222
	kcmil(Cardinal);650mm2(Vienna);690mm2(Budapest);710mm2(Prague)

Conductor - ACCC Str Size Range	1222 kcmil(Cardinal)-710mm²(Prague)
---------------------------------	-------------------------------------

## Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	UI
UL Listed	No

## Logistics

Carton Quantity	4
Minimum Pack Quantity	1
Pallet Quantity	288

## Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section I - Transmission](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 10093976](#)
- [Specifications - BYNA49RT15HACCC](#)