

BS14, Vinyl Splice, #16-14 AWG

By Burndy
Catalog # BS14



Vinyl Splice For 16 - 14 AWG.

Features

- Manufactured from seamless electrolytic copper tubing to provide maximum conductivity and tensile strength in a high quality design with no seams to split
- Funnel entry for easy wire insertion
- Electro-tin plating provides durable, long lasting resistance to corrosion
- Expanded insulation support to lower inventory requirements
- Vinyl insulation provides an economical means of providing high dielectric values and cable insulation support

Application

For Accommodating A Broad Range Of 600 Volt Cables

General

Catalog Number	BS14
Color Code	Blue
Connector Type	Seamless Butt Splice
EU RoHS Indicator	Yes
Insulation	Y
Insulation Type	Vinyl
Material	Copper
Plated	Y
Plating Type	Tin
Sub Brand	VINYLINK
Temperature Rating	105
Trade Name	VINYLINK™
Type	BS
UPC	781810805688
UPC 12 Digit	7818108056888

Dimensions

Dimension - Diameter Max Size inch	0.18 in
Dimension - Length Overall inch	1.00 in
Dimension - Outside Diameter inch	0.18 in
Dimension - Strip Length inch	1/4 in

Electrical Ratings

Voltage - Maximum 600 V

Conductor Related

Conductor - Copper Solid Size Range	16 AWG-14 AWG
Conductor - Copper Str Size Range	16 AWG-14 AWG
Conductor Size	16 - 14 AWG
Conductor Type	CU C Str-Size

Certifications And Compliance

Buy American Compliant	Yes
Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	1000
Minimum Pack Quantity	1000
Pallet Quantity	99999

Product Assets

- [3D Models - BS14_MODEL-STEP](#)
- [3D Models - BS14_MODEL-IGES](#)
- [3D Models - BS14_MODEL-PDF](#)
- [Catalogs - BURNDY Master Catalog - Section B - Small Compression](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_KTFBS_LineArt](#)
- [Sales Drawings - 50094190](#)
- [Specifications - BS14](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRDY-BS14-SPEC-EN | REV 10/2024