



BYNA52RT15HT, Compression Terminal, 15 Degree, 1113-1351.5 kcmil ACSS



By Burndy
Catalog # [BYNA52RT15HT](#)

BURNDY; HYLUG; BYNA-RT15HT, EHV; Features: 15 Deg Compression terminal for 250 Deg C ACSS transmission lines at 345 kV and over; For ACSS Conductor; RoHS Under Investigation; Conductor Range (Main/Primary): 1113 (54-19 Str) - 1351.5 KCMIL ACSS.

General

Catalog Number	BYNA52RT15HT
Connector Type	Splice
UPC	781810490860
UPC 12 Digit	7818104908600

Dimensions

Dimension - D inch	3.95 in
Dimension - Length Overall inch	16.81 in
Dimension - Pad Width inch	3.22 in

Conductor Related

Conductor - ACSS Str Size	1113 (54/19)kcmil;1192.5 (45/7)kcmil;1272 (45/7)kcmil;1272(54/19)kcmil;1351.5(45/7)kcmil;1351.5(54/19)kcmil
Conductor - ACSS Str Size Range	1113 (54/19)kcmil-1351.5(54/19)kcmil

Certifications And Compliance

Standards - RoHS Compliance UI Status

Logistics

Minimum Pack Quantity 1

Product Assets

- [3D Models - BYNA52RT15HT_MODEL-STEP](#)
- [3D Models - BYNA52RT15HT_MODEL-PDF](#)
- [3D Models - BYNA52RT15HT_MODEL-IGES](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section I - Transmission](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 10092588](#)
- [Specifications - BURNDY_BYNA52RT15HT](#)
- [Specifications - BURNDY_BYNA52RT15HT_Specsheet](#)