




BTCGC4SS, Aluminum Ground Tray Clamp, #14-#4 AWG

By Burndy
Catalog # [BTCGC4SS](#)

Aluminum ground tray clamp, accomodates ground wire size #14 AWG to 4 AWG



Features

- Tin plated aluminum for durable, long lasting corrosion resistance
- cULus 467 Listed for Grounding and Bonding in US and Canada
- cULus 2703 Listed for solar PV applications in US and Canada
- Accommodates most popular styles of cable tray with inside or outside flange
- Quick and easy installation
- no drilling or special tools required
- Set screw bonds clamp to the cable tray while another set screw securely fastens the grounding conductor to the clamp providing vibration resistance and outstanding pull-out values
- Grounding green hardware as required in Section 8.4 of UL2703

Application

Type BTCGC-SS clamps are suitable for outdoor applications and may be used with most types of cable tray with an inside or outside flange design

General

EU RoHS Indicator	Contact Manufacturer
Finish Type	Tin Plated
Hex Size	1/4 in
Material	Aluminum
Material - Hardware	Stainless steel
UPC	621945546479

Dimensions

Dimensions	1.35 in x 0.50 in x 1.30 in
Height	1.3 in
Length	1.35 in
Thickness - Flange Plate	1/4 in
Width	0.5 in

Conductor Related

Conductor - AL Str Size Range	#14 - #4 AWG
Conductor - Copper Str Size Range	14 AWG - 4 AWG
Conductor Range	#14 - #4 AWG AL-CU

Certifications And Compliance

Certified Listed	cULus Listed
------------------	--------------

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Sales Drawings - 50097483](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-BTCGC4SS-SPEC-EN | REV 5/2024