



BYNA59R15HT, Compression Terminal Pad Assembly, 2156-2167 kcmil ACSS

By Burndy
Catalog # [BYNA59R15HT](#)



HYLUG™ Terminal Pad Assembly (ACCC), 2156 kcmil-2167 kcmil ACSS.

General

Catalog Number	BYNA59R15HT
Connector Type	Terminal
Die Index	735
Installation Torque	300 in-lb
Recommended in-lb	
Trade Name	HYLUG™
UPC	781810487235
UPC 12 Digit	7818104872355

Dimensions

Dimension - D inch	3.95 in
Dimension - Hole Size inch	0.56 in
Dimension - L Length Overall mm	456 mm
Dimension - Length Overall inch	17.95 in
Dimension - Outside Diameter inch	2.50 in
Dimension - Pad Width inch	3.57 in
Physical Attribute - Tongue Angle	Straight

Conductor Related

Conductor - ACSS Str Size	2156 kcmil-2167 kcmil
Conductor - ACSS Str Size Range	2156(84/19) kcmil-2167(72/7) kcmil

Certifications And Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	UI

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Catalogs - BURNDY Master Catalog - Section I - Transmission Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_BYNA-RHT_LINEART_BW](#)
[Sales Drawings - 10113639](#)
[Specifications - BYNA59R15HT](#)