



# BYNA325MM2T15ACCC, Terminal with TMH24 Hardware Kit, for Amsterdam 380 ACCC, 15 Degree Pad



By Burndy  
Catalog # [BYNA325MM2T15ACCC](#)

HYLUG™ TERMINAL With Hardware Kit TMH24, CTC NO. 600-253-4, Accomodates AMSTERDAM 380 ACCC®, BURNDY DIE 725, 15 Degree Pad Orientation, OVER-LAP CRIMPS.

## Application

For ACCC Conductor, Corona free operation up to 230 KV

## General

Catalog Number	BYNA325MM2T15ACCC
Connector Type	Terminal
Die Index	725
Die Type	L725
Feature - Barrel Style	Tapered
Installation Torque	300 in-lb
Recommended in-lb	
Material	Aluminum
Physical Attribute - Number of Holes	4
Physical Attribute - Pad Orientation	15 Degree
Prefilled Oxide Inhibitor	N
Trade Name	HYLUG™
UPC	781810480427
UPC 12 Digit	7818104804277

## Dimensions

Dimension - D inch	3.95 in
Dimension - F Width Center to Center inch	1.75 in
Dimension - Hole Size inch	0.56 in
Dimension - Outside Diameter inch	1.14 in
Dimension - Pad Width inch	3.22 in
Weight	2 lb

## Electrical Ratings

Voltage - Maximum	230 kV
-------------------	--------

## Conductor Related

Conductor - ACCC Str Size	AMSTERDAM 380 mm <sup>2</sup>
Conductor - Material	Aluminum

## Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Carton Quantity	4
Minimum Pack Quantity	1
Pallet Quantity	288

## Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 50081943](#)
- [Specifications - BYNA325MM2T15ACCC](#)