

CP2929, Heavy Duty Parallel Connector, Copper, A=250 kcmil, B=250 kcmil

By Burndy
Catalog # [CP2929](#)



Features

- High strength, high copper alloy
- Recommended for heavy duty parallel connections
- Silicon bronze hardware and cast copper body provides corrosion resistant assembly
- Long contact surface provides excellent full conductivity

General

Catalog Number	CP2929
Material	Copper Alloy
Plated	N
Plating Type	Unplated
UPC	781810892008
UPC 12 Digit	7818108920088

Dimensions

Dimension - B Length fraction	4 in
Dimension - B Length inch	4 in
Dimension - Height mm	0 mm
Dimension - Width fraction	2 in
Dimension - Width inch	2 in

Conductor Related

Conductor - Copper Str Size A	250 kcmil
Conductor - Copper Str Size A Range	250 kcmil

Conductor - Copper Str Size B	250 kcmil
Conductor - Copper Str Size B Range	250 kcmil

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	EX
Status	
UL Listed	No

Logistics

Minimum Pack Quantity	4
-----------------------	---

Product Assets

- [Catalogs - BURNDY Master Catalog - Section H - Overhead Distribution](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_CP_LineArt](#)
- [Sales Drawings - SA008893-01](#)
- [Specifications - CP2929](#)