



BYNA39RT15ACCC, Terminal Pad Assembly for 713 kcmil, 330mm, 380mm ACCC, 15 Degree Angle



By Burndy
Catalog # [BYNA39RT15ACCC](#)

HYLUG™ Terminal Pad Assembly (ACCC), 713 kcmil,330mm²,380mm² ACCC, 15°, 230kV.

General

Catalog Number	BYNA39RT15ACCC
Connector Type	Terminal
Die Index	722
Installation Torque	300 in-lb
Recommended in-lb	
Material	Aluminum
Trade Name	HYLUG™
UPC	781810476000
UPC 12 Digit	7818104760000

Dimensions

Dimension - D inch	4.50 in
Dimension - Hole Size inch	0.56 in
Dimension - Inside Diameter inch	0.97 in
Dimension - L Length Overall mm	411 mm
Dimension - Length Overall inch	16.2 in
Dimension - Outside Diameter inch	1.50 in
Dimension - Pad Width inch	3.25 in
Physical Attribute - Tongue Angle	15 Degree

Conductor Related

Conductor - ACCC Str Size	713 kcmil(Dove);330mm ² (Oslo);380mm ² (Amsterdam)
---------------------------	---

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

- [3D Models - BYNA39RT15ACCC_MODEL-PDF](#)
- [3D Models - BYNA39RT15ACCC_MODEL-STEP](#)
- [3D Models - BYNA39RT15ACCC_MODEL-IGES](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 10093976](#)
- [Specifications - BYNA39RT15ACCC](#)