

Substation - Aluminum Parallel Groove Clamp

By Burndy
Catalog # CP39A39ASS



Substation Connectors.

Features

- Cast Aluminum Parallel Groove Clamp with Aluminum Hardware
- Recommended for tap or parallel connections
- High strength, high conductivity
- Long contact surface for excellent contact and full conductivity
- PENETROX™ joint compound recommended for all combinations

Application

Substation

General

Catalog Number	CP39A39ASS
Connector Type	Spacer
Installation Torque	480 lb-in
Recommended in-lb	
Material	Aluminum Alloy, Cast
Material - Hardware	Stainless Steel
Plated	N
Plating Type	Unplated
UPC	781810499405
UPC 12 Digit	7818104994055

Dimensions

Dimension - Height inch	3.32 in
Dimension - Height mm	0 mm
Dimension - L Length Overall mm	133.35 mm
Dimension - Length Overall inch	5.25 in
Dimension - Width mm	76 mm

Conductor Related

Conductor - ACSR Str Size	605 (26/7) kcmil;636 (24/7) kcmil;636 (26/7) kcmil;605 (30/19) kcmil;665.6 (24/7) kcmil;636 (30/19) kcmil
Conductor - ACSR Str Size Range	605 (26/7) kcmil-665.6 (24/7) kcmil
Conductor - AL Str Size	700 kcmil;715.5 kcmil;750 kcmil
Conductor - AL Str Size Range	700 kcmil-715.5 kcmil
Physical Attribute - Number of Conductors Accommodated Total	2

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	90
-----------------------	----

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_CP_PARA_CLAMP_LineArt](#)
[Sales Drawings - SD..028518-01](#)
[Specifications - CP39A39ASS](#)