



## BYNA39RT15HACCC, Terminal Pad Assembly for 713 kcmil, 330mm, 380mm ACCC, 15 Degree Angle



By Burndy

Catalog # [BYNA39RT15HACCC](#)

HYLUG™ Terminal Pad Assembly (ACCC) with TMH24 Hardware Kit, 713 kcmil,330mm²,380mm² ACCC, 15°, 230kV.

### General

Catalog Number	BYNA39RT15HACCC
Connector Type	Terminal
Die Index	722
Installation Torque Recommended in-lb	300 in-lb
Material	Aluminum
Trade Name	HYLUG™
UPC	781810474600
UPC 12 Digit	7818104746000

### Dimensions

Dimension - D inch	4.50 in
Dimension - Hole Size inch	0.56 in
Dimension - Inside Diameter inch	0.97 in
Dimension - L Length Overall mm	411 mm
Dimension - Length Overall inch	16.2 in
Dimension - Outside Diameter inch	1.50 in
Dimension - Pad Width inch	3.25 in
Physical Attribute - Tongue Angle	15 Degree

### Conductor Related

Conductor - ACCC Str Size	713 kcmil(Dove);330mm2(Oslo);380mm2
---------------------------	-------------------------------------

### Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	UI
Status	
UL Listed	No

### Logistics

Carton Quantity	4
Minimum Pack Quantity	1
Pallet Quantity	288

### Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section I - Transmission](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 10093976](#)
- [Specifications - BYNA39RT15HACCC](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
BRDY-BYNA39RT15HACCC-SPEC-EN | REV 10/2024