



BYNA43RT15ACCC, Terminal Pad Assembly for 816 kcmil-430mm ACCC, 15 Degree, 230kV

By Burndy
Catalog # [BYNA43RT15ACCC](#)



HYLUG™ Terminal Pad Assembly (ACCC), 816 kcmil-430mm² ACCC, 15°, 230kV.

General

Connector Type	Terminal
Die Index	724
Feature - Barrel Style	Tapered
Installation Torque Recommended in-lb	300 in-lb
Material	Aluminum
Physical Attribute - Number of Holes	4
Trade Name	HYLUG™
UPC	781810514313
UPC 12 Digit	7818105143133

Dimensions

Dimension - Bolt Size fraction	1/2
Dimension - D inch	4.5 in
Dimension - F Width Center to Center inch	1.75 in
Dimension - Hole Size inch	0.56 in
Dimension - Inside Diameter inch	1.05 in
Dimension - Length Overall inch	16.2 in
Dimension - N inch	1.12 in
Dimension - Outside Diameter inch	1.61 in
Dimension - Pad Width inch	3.25 in
Dimension - Thread Size	1/2
Physical Attribute - Tongue Angle	15 Degree

Conductor Related

Conductor - ACCC Str Size	816 kcmil(Grosbeak);430mm ² (Brussels)
Conductor - ACCC Str Size Range	816 kcmil(Grosbeak)-430mm ² (Brussels)

Certifications And Compliance

Standards - RoHS Compliance UI Status

Logistics

Minimum Pack Quantity 1

Product Assets

[3D Models - BYNA43RT15ACCC_MODEL-IGES](#)
[3D Models - BYNA43RT15ACCC_MODEL-STEP](#)
[3D Models - BYNA43RT15ACCC_MODEL-PDF](#)
[Catalogs - Full Line BURNDY Catalog](#)
[Sales Drawings - 10093976](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-BYNA43RT15ACCC-SPEC-EN | REV 5/2024