



EP101HP electric pump with foot control

By Burndy
Catalog # EP101HPFC

Pump, EP101HP, 10K psi, Foot Control.



Features

- Foot Control

Application

Pumping

General

Application - For Use On	Use with 10,000 psi Remote Hydraulic Crimpers and Cutters
Catalog Number	EP101HPFC
Power Source	1 HP 115/230V-AC; 60 Hz Motor
Tool Type	Pump, Electric Hydraulic
Type	Pump
UPC	781810095294
UPC 12 Digit	7818100952944

Dimensions

Dimensions	18.50 in x 11.75 in x 18.75 in
Height	18.75 in
Length	18.5 in
Weight	72 lb
Width	11.75 in

Electrical Ratings

Current Draw Max 10 Amperes

Certifications And Compliance

Standards - RoHS Compliance EX
Status

Logistics

Minimum Pack Quantity 1
Package Contents Pump, Foot Control

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_EP10_LineArt](#)
[Sales Drawings - 20789405](#)
[Specifications - EP101HPFC](#)