



Electric / Hydraulic Pump With Remote Pendant Control Switch and Quick Disconnect Fittings, 10,000 psi, 1/2 HP, 115V AC Motor

By Burndy
Catalog # [EPP10QD](#)

Pump, 10K psi, Remote Pendant Control Switch and QD, 1/2 HP, 115V AC Motor.



Application

Pumping

General

Application - For Use On	Use with 10,000 psi Remote Hydraulic Crimpers and Cutters
Power Source	1/2 HP 115V-AC Motor
Tool Type	Pump, Electric Hydraulic
Type	Pump
UPC	781810127568
UPC 12 Digit	7818101275688

Dimensions

Dimensions	8 in x 6 in x 16 in
Height	16 in
Length	8 in
Weight	30 lb
Width	6 in

Electrical Ratings

Current Draw Max 12.5 Amperes

Certifications And Compliance

Standards - RoHS Compliance CM Status

Logistics

Minimum Pack Quantity 1
Package Contents Pump, Pendant Switch, Quick Disconnects

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - SE207896-01](#)
[SDS - ALFLUID SDS](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-EPP10QD-SPEC-EN | REV 6/2024