



BYNA451R15HHT, Single Pad Compression Deadend for ACSS Conductor, 15 Degree NEMA Tap Pad, includes Hardware



By Burndy
Catalog # [BYNA451R15HHT](#)

BURNDY; HYLUG; BYNA-R-HHT, Kit; Features: Single pad Full tension compression deadend for 250 Deg C rated ACSS transmission lines up to and including 230kV; Standard 15 Deg NEMA tap pad provides either 0 Deg or 30 Deg tap when BYNA-R15 terminal is used; with Hardware; For ACSS Conductor; RoHS Under Investigation.

General

Catalog Number	BYNA451R15HHT
Connector Type	Terminal
Material	Aluminum
Physical Attribute - Number of Holes	4
UPC	781810497449
UPC 12 Digit	7818104974499

Dimensions

Dimension - D inch	3.95 in
Dimension - F Width Center to Center inch	1.75 in
Dimension - Hole Size fraction	14/25
Dimension - Hole Size inch	0.56 in
Dimension - Length Overall inch	15.1 in
Dimension - N inch	0.62 in
Dimension - Outside Diameter inch	1.8 in
Dimension - Pad Width inch	3.22 in

Conductor Related

Conductor - ACSS Str Size	715.5 (24/7) kcmil;715.5 (26/7) kcmil;715.5 (30/19) kcmil;795 (42/7) kcmil;795 (20/7) kcmil;795 (45/7) kcmil;795 (22/7) kcmil;795 (24/7) kcmil;795 (54/7) kcmil;795 (26/7) kcmil;795 (30/19) kcmil
Conductor - ACSS Str Size Range	715.5 (24/7) kcmil-795 (30/19) kcmil

Certifications And Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	CM

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 10113639](#)
- [Specifications - BYNA451R15HHT](#)