

# FCB644N, Substation - Copper Tap Adapter

By Burndy  
Catalog # [FCB644N](#)

Transformer tap adapter, Tin plated, For Cu & Al.



## Features

- Cast in one piece copper alloy
- Transformer tap adapter designed to accommodate NEMA drilled terminals taps from a single secondary transformer outlet
- Tin-Plated

## Application

Substation

## General

Catalog Number	FCB644N
Connector Type	T-Connector
EU RoHS Indicator	Yes
Material	Copper
Physical Attribute - Number of Holes	4
Plated	Y
Plating Type	Tin
Sub Brand	TAP ADAPTER
Type	T-Connector
UPC	781810188019
UPC 12 Digit	7818101880199

## Dimensions

Dimension - Height fraction	5-3/4 in
Dimension - Height inch	5.75 in
Dimension - Height mm	146.1 mm
Dimension - L Length Overall mm	102 mm
Dimension - Length Overall inch	4.00 in
Dimension - P inch	2.75 in

Dimension - Pin Diameter fraction 3/4 in

Dimension - Pin Diameter inch .75 in

## Conductor Related

Conductor Type	<ul style="list-style-type: none"> <li>• CU C Str-Size</li> <li>• CU C Solid-Size</li> </ul>
----------------	--

## Certifications And Compliance

Buy American Compliant	Contact Manufacturer
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Certified Listed	BABA Compliant (All status valid till December 2024)
Standards - RoHS Compliance Status	EX
UL Listed	No

## Logistics

Minimum Pack Quantity	1
-----------------------	---

## Product Assets

- [3D Models - FCB644N\\_MODEL-IGES](#)
- [3D Models - FCB644N\\_MODEL-PDF](#)
- [3D Models - FCB644N\\_MODEL-STEP](#)
- [Catalogs - BURNDY Master Catalog - Section A - Mechanical](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR\\_FCB634N\\_LineArt](#)
- [Sales Drawings - SE210547-01](#)
- [Specifications - FCB644N](#)