



BYNA451RT15ACCC, Terminal Pad Assembly, 540mm ACCC, 15 Degree, 230kV

By Burndy
Catalog # [BYNA451RT15ACCC](#)



HYLUG™ Terminal Pad Assembly (ACCC), 540mm² ACCC, 15°, 230kV.

General

Connector Type	Terminal
Die Index	725
Feature - Barrel Style	Tapered
Installation Torque Recommended in-lb	300 in-lb
Material	Aluminum
Physical Attribute - Number of Holes	4
Trade Name	HYLUG™
UPC	781810514375
UPC 12 Digit	7818105143755

Dimensions

Dimension - Bolt Size fraction	1/2
Dimension - D inch	3.95 in
Dimension - F Width Center to Center inch	1.75 in
Dimension - Hole Size inch	0.56 in
Dimension - Inside Diameter inch	1.18 in
Dimension - L Length Overall mm	381 mm
Dimension - Length Overall inch	15 in
Dimension - N inch	0.63 in
Dimension - Outside Diameter inch	1.8 in
Dimension - Pad Width inch	3.22 in
Dimension - Thread Size	1/2
Physical Attribute - Tongue Angle	15 Degree

Conductor Related

Conductor - ACCC Str Size	540mm ² (Dublin)
Conductor - ACCC Str Size Range	540mm ² (Dublin)

Certifications And Compliance

Standards - RoHS Compliance CM Status

Logistics

Minimum Pack Quantity 1

Product Assets

[3D Models - BYNA451RT15ACCC_MODEL-IGES](#)
[3D Models - BYNA451RT15ACCC_MODEL-PDF](#)
[3D Models - BYNA451RT15ACCC_MODEL-STEP](#)
[Catalogs - Full Line BURNDY Catalog](#)
[Sales Drawings - 50068519](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-BYNA451RT15ACCC-SPEC-EN | REV 5/2024