



BYNA49R15HHT, Single Pad Full Tension Compression Deadend, 15 Degree NEMA Tap Pad, 1033.5 ACSS, includes Hardware

By Burndy
Catalog # [BYNA49R15HHT](#)



BURNDY; HYLUG; BYNA-R-HHT, Kit; Features: Single pad Full tension compression deadend for 250 Deg C rated ACSS transmission lines up to and including 230kV; Standard 15 Deg NEMA tap pad provides either 0 Deg or 30 Deg tap when BYNA-R15 terminal is used; with Hardware; For ACSS Conductor; RoHS Compatible.

General

Connector Type	Terminal
Trade Name	HYLUG™
UPC	781810495810
UPC 12 Digit	7818104958100

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity 1

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - 10113639](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-BYNA49R15HHT-SPEC-EN | REV 6/2024