

# BYNA52RT15HACCC, Terminal Pad Assembly with TMH24 Hardware Kit, 780mm-840mm ACCC, 15 Degree, 230kV



By Burndy  
Catalog # [BYNA52RT15HACCC](#)

HYLUG™ Terminal Pad Assembly (ACCC) with TMH24 Hardware Kit, 780mm²-840mm² ACCC, 15°, 230kV.

## General

Catalog Number	BYNA52RT15HACCC
Connector Type	Terminal
Die Index	728
Installation Torque	300 in-lb
Recommended in-lb	
Material	Aluminum
Trade Name	HYLUG™
UPC	781810474648
UPC 12 Digit	7818104746488

## Dimensions

Dimension - D inch	3.95 in
Dimension - Hole Size inch	0.56 in
Dimension - Inside Diameter inch	1.46 in
Dimension - L Length Overall mm	438 mm
Dimension - Length Overall inch	17.3 in
Dimension - Outside Diameter inch	2.25 in
Dimension - Pad Width inch	3.22 in
Physical Attribute - Tongue Angle	15 Degree

## Conductor Related

Conductor - ACCC Str Size	780mm²(London);1572 kcmil(Bittern);840mm²(Paris)
Conductor - ACCC Str Size Range	780mm²(London)-840mm²(Paris)

## Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Minimum Pack Quantity	1
-----------------------	---

## Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section I - Transmission](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 10093976](#)
- [Specifications - BYNA52RT15HACCC](#)