



BYNA56RT15HHT, ACSS - Compression Terminal

By Burndy

Catalog # [BYNA56RT15HHT](#)



BURNDY; HYLUG; BYNA-RT-HHT, EHV; Features: Terminal and hardware; Full tension compression deadend for 250 Deg C rated ACSS transmission lines at 345 kV and over; 15 Deg NEMA Tap Pad Terminal; For ACSS Conductor; RoHS Compatible; Conductor Range (Main/Primary): 1510.5 -1590 KCMIL ACSS.

General

Catalog Number	BYNA56RT15HHT
Connector Type	Terminal
Trade Name	HYLUG™
UPC	781810509920
UPC 12 Digit	7818105099200

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No

Logistics

Carton Quantity	4
Minimum Pack Quantity	1
Pallet Quantity	288

Product Assets

- [3D Models - BYNA56RT15HHT_MODEL-STEP](#)
- [3D Models - BYNA56RT15HHT_MODEL-IGES](#)
- [3D Models - BYNA56RT15HHT_MODEL-PDF](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 10092588](#)
- [Specifications - BYNA56RT15HHT](#)