



FD657T0144NSV, Substation - Copper Stud Connector

By Burndy
Catalog # [FD657T0144NSV](#)



Copper Stud Connectors.

Application

Substation

General

Catalog Number	FD657T0144NSV
Connector Type	Stud Connector
Material	Copper Alloy
Material - Hardware	DURIUM™ Silicon Bronze
Physical Attribute - Number of Holes	4
Physical Attribute - Pad Configuration	4x4 - 4 holes
Physical Attribute - Pad Orientation	In-line
Plated	Y
Plating Type	Silver
Type	Studs
UPC	621945114128
UPC 12 Digit	6219451141288

Dimensions

Dimension - B Length inch	2.00 in
Dimension - Bolt Size fraction	3/8
Dimension - D inch	4.00 in
Dimension - F Width Center to Center inch	1.75 in

Dimension - L Length Overall mm	168 mm
Dimension - Length Overall inch	6.62 in
Dimension - N inch	1.12 in
Dimension - Pad Width inch	4.00 in
Dimension - Pin Diameter fraction	1-9/50 in
Dimension - Pin Diameter inch	1.180 in
Dimension - Thread Size	3/8-0

Conductor Related

Conductor - Connection Combination	Stud to Bar
------------------------------------	-------------

Certifications And Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	UI

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Specifications - FD657T0144NSV](#)