



BYNA56RT15HT, Compression Terminal, 15 Degree, High Temperature, 1510.1-1590 kcmil ACSS



By Burndy
Catalog # [BYNA56RT15HT](#)

BURNDY; HYLUG; BYNA-RT15HT, EHV; Features: 15 Deg Compression terminal for 250 Deg C ACSS transmission lines at 345 kV and over; For ACSS Conductor; RoHS Compatible; Conductor Range (Main/Primary): 1510.5 -1590 KCMIL ACSS.

General

Catalog Number	BYNA56RT15HT
Connector Type	Splice
UPC	781810490877
UPC 12 Digit	7818104908777

Dimensions

Dimension - D inch	3.95 in
Dimension - Length Overall inch	17.56 in
Dimension - Pad Width inch	3.44 in

Conductor Related

Conductor - ACSS Str Size	1510.5(45/7)kcmil;1510.5(54/19)kcmil;1590(45/7)kcmil;1590(54/19)kcmil
Conductor - ACSS Str Size Range	1510.5(45/7)kcmil-1590(54/19)kcmil

Certifications And Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	4
Minimum Pack Quantity	1
Pallet Quantity	288

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section I - Transmission](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 10092588](#)
- [Specifications - BYNA56RT15HT](#)